

#### **Technical Data Sheet**

Head Office : 241, Hae Yang-Ro, Yeong Do-Gu, Busan, Korea Tel +82-51-403-6441 Fax +82-51-403-6440 Ulsan Plant : 91, Cheoyong-Ro 616 Beon-Gil, Nam-Gu, Ulsan, Korea Tel +82-52-256-7857 Fax +82-52-256-4070

# **LUXMOL 10**

## White Mineral Oil (Pharmaceutical Grade)

## **Product Description**

**LUXMOL 10** is a product that meets and follows the strict requirement of the pharmaceutical regulations in each country. The product has an excellent quality, which are produced in GMP qualified plant that ensures high safety and stability by special treatment and packing process for sterilizing high-purity raw materials.

\*The facility designed with SUS 316

## **Typical Application**

- Gelatine capsules for medical treatments
- Ointments and salves
- Animal vaccines
- Other uses for medical treatments (if relevant)

#### **Features**

- HACCP certified
- HALAL certified
- KOSHER certified
- USA FDA, 21 CFR 172.878, 178.3620(a), White Mineral Oil certified
- US Pharmacopeia, European Pharmacopeia passed
- EU REACH (EC number 232-455-8) registered
- CAS No: 8042-47-5 (White Mineral Oil)

## **Package Sizes**

- 200L STEEL DRUM
- 24.000L IN ISO TANK
- 24,000L IN FLEXIBAG

## **Health and Safety**

-Detailed health and safety information for this product is provided in the Material Safety Data Sheet (MSDS), available upon request.



## **Technical Data Sheet**

Head Office : 241, Hae Yang-Ro, Yeong Do-Gu, Busan, Korea Tel +82-51-403-6441 Fax +82-51-403-6440 Ulsan Plant : 91, Cheoyong-Ro 616 Beon-Gil, Nam-Gu, Ulsan, Korea Tel +82-52-256-7857 Fax +82-52-256-4070

## **Product Specification & Typical Properties**

Typical Properties	Test Method	Specification	Typical
Appearance	VISUAL	Oily liquid nearly free from	Oily liquid nearly free from
		fluorescence, clear bright, free of	fluorescence, clear bright, free
		any haze, turbidity, free from	of any haze, turbidity, free from
		foreign matter contamination or	foreign matter contamination or
		water droplets	water droplets
Infrared Absorption	USP	The IR spectrum of the sample	
		shall exhibit absorption bands of	
		the same pattern and placement as	pass
		those exhibited by the standard,	
		with no extraneous bands present.	
Odour	-	Odourless	Odourless or very faint oil odour
Colour, Saybolt	ASTM D 156	Min +30	+30
Density 15°C, g/cm	ASTM D 4052	Report	0.8350
Flash point °C	ASTM D 92	Min 210	230
Pour point °C	ASTM D 97	Max -9.0	-15.0
Viscosity, SUS @ 100°F	ASTM D 2161	Min 95	100
Viscosity @ 40°C, mm²/s	ASTM D 445	$18.5 \sim 21.5$	20.00
Refractive Index @20°C	ASTM D 1218	Report	1.4620
Acidity	USP	No more than 0.1mL of 0.01N	
		Sodium	Pass
		Hydroxide required to change the	1 455
		colour to pink	
Solid Paraffin	USP	A black line of 0.5nm width drawn	Pass
		on a piece of white paper, held	
		vertically behind the bottle, should	
		be clear visible	
Limit of Sulphur Compounds	USP	No dark brown colour should	Pass
		develop	
UV Absorbance 260-350nm	ASTM D 2269	Max 0.1	0.020
Readily Carburizable Substances, 95% H <sub>2</sub> SO <sub>4</sub>	ASTM D 565	The oil should remain colourless or	Pass
		show a slight yellow colour, and	
		the acid will not be darker than the	
		colour produced by the standard	

